

6 ft USB to DB25 Parallel Printer Adapter Cable - M/F

Product ID: ICUSB1284D25



The ICUSB1284D25 6 ft USB to DB25 Parallel Printer Adapter Cable turns an available USB port on a host PC into a DB25 Female Parallel port - allowing you to connect a DB25 printer to the computer as if the necessary parallel port was built-on.

A cost-effective and reliable solution, the USB to DB25 adapter saves the expense of replacing a parallel printer for the sake of USB capability.

Backed by a StarTech.com 2-year warranty and free lifetime technical support .

Certifications, Reports and Compatibility

Applications

- Allows you to quickly add a parallel port to your computer for use with printers with DB25 connectors
- Ideal solution for notebooks or desktops without a Parallel port

Features

- Fully Plug & Play for easy installation
 - USB bus-powered operation, no external power adapter required
 - Eliminates the need for manual or automatic parallel switch boxes
-

Hardware

Warranty	2 Years
Ports	1
Interface	Parallel
Bus Type	USB 2.0
Chipset ID	Prolific - PL2305

Performance

Maximum Data Transfer Rate	1.5Mbps
----------------------------	---------

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	DB-25 (25 pin, D-Sub)

Software

OS Compatibility	Windows 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2000, 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 macOS 10.6 to 10.15, 11.0 Linux 2.6.x to 4.11.x <i>LTS Versions only</i>
------------------	--

Environmental

Operating Temperature	5C to 40C (41F to 140F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~80% RH non-condensing

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	3.9 oz [110.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.9 in [22.0 mm]
Shipping (Package) Weight	4.2 oz [119.0 g]

What's in the Box

Included in Package	USB to Parallel Adapter Cable
---------------------	-------------------------------

****Product appearance and specifications are subject to change without notice.***

