

VGA Video Extender over Cat 5 Remote Receiver with Audio

Product ID: STUTPEALR



The STUTPEALR VGA Video Extender over Cat 5 Remote Receiver with Audio is the receiver unit utilized by our STUTPEA VGA and Audio over Cat 5 extension series. This convenient video distribution system simplifies the implementation of digital signage solutions by allowing a single VGA source and corresponding audio to be broadcast to multiple displays at up to 300m (950ft) away.

Comprised of one receiver unit per display, and either a ST124UTPEA 4 port VGA & Audio extender or ST128UTPEA 8 port VGA & Audio extender unit, the VGA and Audio extension series can transmit a single VGA output and corresponding audio to four or eight displays/receivers over standard Cat 5 or better UTP cable.

For even more versatility, you also have the option to multiply the amount of remote displays in your setup by adding the STUTPEA4X VGA & Audio over Cat 5 Line Splitter to your setup allowing your VGA and accompanying audio signal to be broadcast to up to a total 16 displays.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard
- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites

- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at trade-shows and in auditoriums

Features

- Send video and audio over Cat5 or better cabling to remote displays
- Monitors can be situated up to 300m / 950ft away at a resolution of 1280x1024 / 720p
- Supports maximum resolutions of up to 1920x1080 / 1080p @ 75m / 250ft
- Choice of using a 4 or 8 port transmitter/extender unit – sold separately
- No software or drivers required
- Adjustable EQ and Gain

Hardware

| | |
|-------------|---------------------|
| Warranty | 2 Years |
| Ports | 1 |
| Cabling | Cat 5 UTP or better |
| Audio | Yes |
| Daisy-Chain | Yes |

Performance

| | |
|-----------------------|--|
| Max Distance | 300 m / 950 ft |
| Supported Resolutions | 1920x1200 @ 75m(250ft) 1440x900 @ 150m(500ft) 1024x768 @ 300m(950ft) |
| Wide Screen Supported | Yes |

Connector(s)

| | |
|------------------------|--|
| Remote Unit Connectors | VGA (15 pin, High Density D-Sub) 3.5 mm Mini-Jack (3 Position) RJ-45 |
|------------------------|--|



Power

| | |
|------------------------------|---------------------|
| Power Source | AC Adapter Included |
| Output Voltage | 12V DC |
| Output Current | 0.6A |
| Center Tip Polarity | Positive |
| Plug Type | M |
| Power Consumption (In Watts) | 7.2 |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 50C (32F to 122F) |
| Storage Temperature | -20C to 70C (-4F to 158F) |
| Humidity | 5~90% RH |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Black |
| Material | Aluminum |
| Product Length | 5.1 in [13 cm] |
| Product Width | 4.4 in [11.0 cm] |
| Product Height | 1.0 in [25 mm] |
| Weight of Product | 10.3 oz [293 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 9.4 in [24 cm] |
| Package Width | 2.8 in [70 mm] |
| Package Height | 6.1 in [15.5 cm] |
| Shipping (Package) Weight | 20.3 oz [575 g] |

What's in the Box

| | |
|---------------------|-------------------------|
| Included in Package | Long Range UTP Receiver |
|---------------------|-------------------------|



Power Adapter

Instruction Manual

****Product appearance and specifications are subject to change without notice.***

