

## 75 ft Cat5e Blue Snagless Shielded RJ45 F/UTP Cat 5e Patch Cable - 75ft Patch Cord

**Product ID:** S45PATCH75BL



StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cables offer reliable Ethernet connections. This 75ft cable meets or exceeds all Category 5e specifications and features a durable blue jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To reduce susceptibility to EMI/RFI and near end cross-talk, the patch cable is shielded throughout the length of the cable, as well as around the RJ45 connectors. Our Cat5e Shielded F/UTP Snagless Patch Cables also feature a snagless design that protects the RJ45 clip from snagging during installation, as well as PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage.

StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cable is constructed of top quality materials (100% copper conductors, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and performance, and backed by our Lifetime Warranty.

### **Certifications, Reports and Compatibility**

#### **Applications**

- Designed for Network Adapters, Hubs, Switches, Routers, DSL/Cable Modems and other applications requiring high-speed cables
- Works with 1000 BASE-T, 100 BASE-T, 10 BASE-T, Token Ring, ATM & ISDN networks
- Suited for industrial applications

#### **Features**

- StarTech.com Category 5e shielded cables are manufactured to meet or exceed CAT5e specifications

- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification

---

**Hardware**

|                       |                             |
|-----------------------|-----------------------------|
| Warranty              | Lifetime                    |
| Number of Conductors  | 4 pair F/UTP                |
| Cable Jacket Material | PVC - Polyvinyl Chloride    |
| Fire Rating           | CMG Rated (General Purpose) |
| Cable Type            | Shielded Snag-less          |

---

**Connector(s)**

|             |       |
|-------------|-------|
| Connector A | RJ-45 |
| Connector B | RJ-45 |

---

**Physical Characteristics**

|                   |                  |
|-------------------|------------------|
| Color             | Blue             |
| Wire Gauge        | 24 AWG           |
| Cable Length      | 75.0 ft [22.9 m] |
| Product Length    | 75.0 ft [22.9 m] |
| Weight of Product | 31.8 oz [900 g]  |

---

**Packaging Information**

|                           |                   |
|---------------------------|-------------------|
| Package Length            | 13.0 in [33 cm]   |
| Package Width             | 10.0 in [25.5 cm] |
| Package Height            | 1.5 in [38 mm]    |
| Shipping (Package) Weight | 32.4 oz [917 g]   |

---

***\*Product appearance and specifications are subject to change without notice.***

