

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - White

**Product ID:** WIRC6PATWHRL



This 1000ft roll of Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

## Certifications, Reports and Compatibility

## Applications

- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network
- Can be used in home, office and other environments

## Features

- Available in various colors for easy identification and color-coding

---

### Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CM Rated

---

## Performance

Cable Rating	CAT6 - 500 MHz
--------------	----------------

---

## Physical Characteristics

Color	White
Wire Gauge	24 AWG
Conductor Type	Stranded Copper
Cable Length	1000.0 ft [304.9 m]
Product Length	1000.0 ft [304.9 m]
Weight of Product	29.3 lb [13.3 kg]

---

## Packaging Information

Package Length	8.2 in [20.8 cm]
Package Width	14.3 in [36.4 cm]
Package Height	14.6 in [37 cm]
Shipping (Package) Weight	29.3 lb [13.3 kg]

---

## What's in the Box

Included in Package	1000ft Roll White Stranded Cat 6 Patch Cable
---------------------	----------------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

