

10 ft Computer Power Cord - C19 to C20

Product ID: PXTC19C2010



This 10 ft Power Cord is a compact C19 to C20 computer cable that is designed to work with racks and Power Distribution Units.

Backed by StarTech.com's Lifetime Warranty, this 10ft computer power cord is expertly designed for longevity, and is constructed of only the highest quality of materials.

Certifications, Reports and Compatibility

Applications

Features

- Rated to carry 250V at 13A
- 16 AWG wire

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector Type(s)	IEC 60320 C19 Power
-------------------	---------------------

IEC 60320 C20 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	250 AC
Input Current	13 A

Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]

Packaging Information

Package Length	1.7 in [42 mm]
Package Width	0.6 in [15 mm]
Package Height	3.8 in [97 mm]
Shipping (Package) Weight	16.6 oz [470 g]

What's in the Box

Included in Package	10 ft Computer Power Cord - C19 to C20
---------------------	--

****Product appearance and specifications are subject to change without notice.***

