




MATERIAL

Housing: High-impact Polycarbonate (PC resin), UL 94 V-2 rated, transparent
Blades: Phosphor bronze, plated with 50 μin (1.27 μm) thick hard gold over 100 μin (2.54 μm) thick nickel underplate on contact area
RoHS compliant

WIRE RANGE

Conductor Diameters: 0.016 in (0.41 mm) 26 AWG - 0.020 in (0.51 mm) 24 AWG
Insulation Diameters: 0.032 in (0.8 mm) - 0.039 in (1.0 mm)
Cable Diameters: 0.197 in (5 mm) - 0.276 in (7 mm)

SPECIFICATION

Meet IEC 60603-7 Standard
Meet TIA-1096-A Standard

Blades	2-prong	Angled 2-prong	Angled 3-prong	Long Angled 3-prong
Drawing				
Mark				
Gold Plating	3 μ "	6 μ "	15 μ "	30 μ "
Mark				

DRAWN BY Ethan Wu		APPROVED BY Jerry Su		DIMENSIONS ARE IN [MM] TOLERANCES:		ANGLE		3rd Angle Projection		DATE		SCALE		SHEET		REV.	
~20		~50		~150		150~		2°		2012.09.03		X		1/1		1	
±0.2		±0.4		±0.5		±1.5											
Another quality product from		BLACK BOX		NETWORK SERVICES		724-746-5500 • www.blackbox.com		TITLE		Category 5e Modular Plugs		Un-Shielded - xxx Pack		PARTS NO.		FMT5E-XXXXPAK	