

6 ft DisplayPort Video Extension Cable - M/F

Product ID: DPEXT6L



The DPEXT6L 6-foot, DisplayPort Video Extension Cable supports 21.6 Gbps bandwidth, giving a full 4K x 2K (3840 x 2400 at 60Hz) resolution and 3D Stereo display (2560 x 1600 at 120Hz). This DP1.2 cable also provides additional features such as High Bit Rate 2 (HBR2), 8 Audio Channels, Multi-Stream Transport (MST) for connecting multiple displays and Global Time Code (GTC) for sub-micro video/audio sync.

This DisplayPort v1.2 Video Extension Cable adds an extra 6ft to any DisplayPort cable. The extension cable features latching connectors with gold-plated pins for superior conductivity and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Extend your DisplayPort interface by 6ft

Features

- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Aluminum-Mylar Foil with Braided Shielding
- Molded latching connectors with strain relief

Hardware

Warranty

Lifetime

Number of Conductors	20
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

Environmental

Operating Temperature	-20C to 80C (-4F to 158F)
Storage Temperature	-25C to 85C (-13F to 185F)
Humidity	40%-70%RH

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.8 in [20.9 mm]
Product Height	0.5 in [12.6 mm]
Weight of Product	3.2 oz [91.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	0.8 in [20.0 mm]
Package Height	7.9 in [20.0 cm]
Shipping (Package) Weight	3.4 oz [96.0 g]



**What's in the
Box**

Included in Package 6 ft DisplayPort Video Extension Cable - M/F

****Product appearance and specifications are subject to change without notice.***

