

Select Plus Cabinets

These cabinets have split mesh rear doors and come with mesh or tempered glass front doors.



FEATURES

- » Weight capacity of 2200 or 1760 pounds.
- » Constructed of 16-gauge steel.
- » Extra-deep (42") models are available.
- » Split mesh rear doors.
- » Server cabinets feature mesh front doors; network cabinets feature tempered glass front doors.
- » Arrive fully assembled and ready to go to work in your data center.
- » Offer versatile mounting with standard 19" M6 rails that work with most Black Box® Cabinet Accessories.
- » Have two sets of adjustable rails, which provide even more versatility.
- » UL® Listed.



Choose the optional 3- or 6-fan unit to keep the air flowing.



Split rear doors for easy access.



Vented top panel

Lockable, removable vented side panels

Choose from tempered glass or mesh front door

Locking, removable front and rear doors

Generous cable access

What's included:

- ◆ Cabinet
- ◆ (4) 2.5" casters
- ◆ (4) leg levelers
- ◆ Mesh or tempered glass front door
- ◆ Mesh split rear door
- ◆ User's manual

TECH SPECS

Rack Units — RM2500A, RM2510A: 15U;
 RM2515A, RM2525A: 24U;
 RM2520A, RM2530A: 38U;
 RM2540A, RM2545A, RM2555A, RM2640A, RM2550A, RM2650A: 42U

Exterior Height — RM2500A, RM2510A: 30.4";
 RM2515A, RM2525A: 46.15";
 RM2520A, RM2530A: 70.7";
 RM2540A, RM2545A, RM2555A, RM2640A, RM2550A, RM2650A: 77.6"

Exterior Width — RM2500A, RM2515A, RM2520A, RM2525A, RM2540A, RM2510A, RM2530A, RM2550A, RM2640A, RM2650A: 24";
 RM2545A, RM2555A: 30"

Exterior Depth — RM2500A, RM2515A, RM2520A, RM2525A, RM2540A, RM2510A, RM2530A, RM2550A: 39.4";
 RM2640A, RM2650A, RM2545A: 42";
 RM2555A: 32"

Interior Width — RM2500A, RM2515A, RM2520A, RM2525A, RM2540A, RM2510A, RM2530A, RM2550A, RM2640A, RM2650A: 21.3";
 RM2545A, RM2555A: 29.3"

Interior Depth — RM2500A, RM2515A, RM2520A, RM2525A, RM2540A, RM2510A, RM2530A, RM2550A: 38.5";
 RM2640A, RM2650A: 41.7";
 RM2545A: 41.5";
 RM2555A: 31.5"

Weight — RM2500A, RM2510A: 190 lb.;
 RM2515A, RM2525A: 240 lb.;
 RM2520A, RM2530A: 323 lb.;
 RM2540A, RM2550A: 340 lb.;
 RM2640A, RM2650A: 343 lb.;
 RM2545A: 332 lb.;
 RM2555A: 293 lb.

Item

Code

Select Plus Cabinets, Mesh Split Rear Door

Server, Mesh Front Door, 2200-lb. Capacity

15U

RM2500A

24U

RM2515A

38U

RM2520A

42U

RM2540A

Server, Extra Deep, Mesh Front Door, 1760-lb. Capacity

42U (42"D, 24"W)

RM2640A

42U (42"D, 30"W)

RM2545A

Network, Tempered Glass Front Door, 2200-lb. Capacity

15U

RM2510A

24U

RM2525A

38U

RM2530A

42U (39.4"D, 24"W)

RM2550A

42U (32"D, 30"W)

RM2555A

Network, Extra Deep, Tempered Glass Front Door

1760-lb. Capacity

42U (42"D, 24"W)

RM2650A

To join two or more Select Plus Cabinets, order...

Multicabinet Joining Kit

RM2407

To ground your Select Plus Cabinets, order...

Grounding Kit

RM2408

To ventilate your Select Plus Cabinets, order...

3-Fan Unit

RM2409

6-Fan Unit

RM2415

You may also need...

Cage Nuts and Screws, 20-Pack, M6, 5/8" Long

RM388