

Miscellaneous Cabinet Shelves

Customize your cabinets
to fit your system.



FEATURES

- » These sturdy shelves fit securely in your cabinets.
- » Arrange your servers or other equipment on shelves installed in a cabinet.
- » Choose solid or vented fixed or vented sliding shelves.

OVERVIEW

Rackmount Solid Fixed Shelves

- Weight capacity of 50 pounds.
- Use 3U of rack space.
- Mount on EIA standard 19" rails.

Rackmount Vented Fixed Shelves

- Weight capacity of 35 or 60 pounds.
- Vented for improved air circulation.
- Use 3U of rack space.
- 18"-deep shelf is available in black or ivory.
- Mounts on EIA standard 19" rails.

Rackmount Vented Sliding Shelves

- Weight capacity of 50 pounds.
- Constructed of 18-gauge steel.
- Measure 4"H x 19"W x 18"D.
- Slide out for easy access.
- Vented for improved air circulation.
- Choose from black or ivory.
- Mount on EIA standard 19" rails.

NOTE: To install the Rackmount Vented Sliding Shelf (RMTS06B, RMTS06I) in a cabinet, you must move the rails from the front of the cabinet to the back.

Rackmount Server Shelves


- Weight capacity of 200 pounds.
- Constructed of 18-gauge steel.
- Mount back-to-back to create a 20" deep shelving area to hold desktop- or tower-style CPUs.
- Measure 19" or 23"W x 10"D.
- Mount on EIA standard 19" or 23" rails.

Vented Center-Weight Shelf

- Weight capacity of 50 pounds.
- Constructed of 16-gauge steel.
- Measures 19"W x 18.5"D.
- Uses 2U of rack space.
- Vented for improved air circulation.
- Mounts on standard EIA 19" rails.

19" Sliding Pivoting Keyboard Tray with Mouse Tray

- Weight capacity of 90 pounds.
- Slide keyboard in sideways for storage.
- To use, simply pull the keyboard out and pivot into position.
- Features adjustable four-point 19" EIA mounting.
- Mouse tray features non-skid surface.
- Use the mouse tray on the left or right.
- Cushioned wrist rest for more comfortable use.
- Holds a keyboard up to 20.5" wide.
- Slides out up to 19".
- Provides the ideal solution for keyboards that are too wide for your cabinet or rack.



TECH SPECS

RMTS04:

Capacity — 50 lb. (22.7 kg)
Steel Gauge — 16
Size — 5.2"H x 19"W x 12"D
(13.2 x 48.3 x 30.5 cm)

RMTS02:

Capacity — 35 lb. (15.9 kg)
Steel Gauge — 18
Size — 5.2"H x 19"W x 12"D
(13.2 x 48.3 x 30.5 cm)

RMTS03:

Capacity — 60 lb. (27.3 kg)
Steel Gauge — 16
Size — 5.2"H x 19"W x 17.75"D
(13.2 x 48.3 x 45.1 cm)

RMTS05B, RMTS05I:

Capacity — 35 lb. (15.9 kg)
Steel Gauge — 18
Size — 5.2"H x 19"W x 18"D
(13.2 x 48.3 x 45.7 cm)

RMTS06B, RMTS06I:

Capacity — 50 lb. (22.7 kg)
Steel Gauge — 18
Size — 4"H x 19"W x 18"D
(10.2 x 48.3 x 45.7 cm)

RMTS07-19, RMTS07-23:

Capacity — 200 lb. (90.9 kg)
Steel Gauge — 18
Size —
RMTS07-19: 3.5"H x 19"W x 10"D
(8.9 x 48.3 x 25.4 cm);
RMTS07-23: 3.5"H x 23"W x 10"D
(8.9 x 58.4 x 25.4 cm)

RMTS08:

Capacity — 50 lb. (22.7 kg)
Steel Gauge — 16
Size — 3.5"H x 19"W x 18.5"D
(8.9 x 48.3 x 47 cm)

RM385:

Capacity — 90 lb. (40.9 kg)
Size — 3.5"H x 20.6"W x 9.5"D
(8.9 x 52.3 x 24.1 cm)

What's included

RMTS02:

- ◆ Rackmount Vented Fixed Shelf
- ◆ (4) #10-32 x 5/8" black truss-head screws
- ◆ (4) #12-24 x 5/8" black truss-head screws
- ◆ (4) cage nuts
- ◆ (4) #10 black nylon washers
- ◆ (4) #12 black nylon washers
- ◆ User's manual

RMTS07-19:

- ◆ Rackmount Server Shelf
- ◆ (8) #10-32 x 1/2" pan-head screws
- ◆ (8) #12-24 x 1/2" pan-head screws
- ◆ User's manual

RM385:

- ◆ 19" Sliding Pivoting Keyboard Tray with Mouse Tray
- ◆ (4) mounting brackets
- ◆ (8) #10-32 screws
- ◆ User's manual

Item	Code
Rackmount Solid Fixed Shelves 12"D, Black 35-lb. Capacity 50-lb. Capacity	RMTS01 RMTS04
Rackmount Vented Fixed Shelves 12"D, 35-lb. Capacity, Black 17.75"D, 60-lb. Capacity, Black 18"D, 35-lb. Capacity Black Ivory	RMTS02 RMTS03 RMTS05B RMTS05I
Rackmount Vented Sliding Shelves 18"D, 50-lb. Capacity Black Ivory	RMTS06B RMTS06I
Rackmount Server Shelves 10"D, 200-lb. Capacity, Black for 19" Rails for 23" Rails	RMTS07-19 RMTS07-23
Vented Center-Weight Shelf 18.5"D, 50-lb. Capacity, Black	RMTS08
19" Sliding Pivoting Keyboard Tray with Mouse Tray	RM385