

## 15 ft DVI-D Single Link Cable - M/M

**Product ID:** DVIDSMM15



The DVIDSMM15 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 15ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

### Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

---

**Connector(s)**

Connector A	DVI-D (19 pin)
Connector B	DVI-D (19 pin)

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Weight of Product	13.7 oz [387 g]

---

**Packaging Information**

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.7 in [44 mm]
Shipping (Package) Weight	14.0 oz [396 g]

---

**What's in the Box**

Included in Package	15 ft DVI-D Single Link Cable - M/M
---------------------	-------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

