

## 2 Port VGA Auto Switch

**Product ID:** ST122VGAU



The ST122VGAU VGA Auto Switcher lets you share a display between two computers and prioritize your VGA signals. The VGA switch features a primary and secondary VGA input port, and automatically outputs the signal from the primary input. When the signal feed connected to the primary input port is cut, the switcher automatically defaults to the video signal on the secondary VGA input port.

Designed for maximum control and versatility, the VGA Auto switcher also offers manual control of connected signals with easy-to-use front panel buttons that allow you to toggle between video sources.

## Certifications, Reports and Compatibility

### Applications

- Ideal for use with a laptop computer and a boardroom projector in meetings and presentations, backup safety control systems, and home A/V switching applications
- Perfect for digital signage applications in retail environments requiring more than one media player or PC to be connected
- Great for connecting/switching multiple sources in Test Bench Facilities, Data Centers, Help Desks and Video Broadcasting Facilities

### Features

- Automatically selects the priority of incoming video signals for display
- Supports resolutions up to 1920x1440

- Easy to use front panel selection buttons
- Easy installation - set up in minutes
- Video Bandwidth 250 MHz
- Rugged steel enclosure
- Supports DDC1, DDC2, DDC2B, DDC2B+, DDC2AB on port 1

---

#### Hardware

Warranty	2 Years
AV Input	VGA
Ports	2
AV Output	VGA
Audio	No
Industry Standards	DDC1, DDC2, DDC2B, DDC2B+, DDC2AB ( DDC Support on Port 1 only)

---

#### Performance

Wide Screen Supported	Yes
Bandwidth	250 MHz
MTBF	80,000 hours

---

#### Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

---

#### Special Notes / Requirements

Note	Port 1 is set to have higher priority than port 2 when both signals are on
------	--

---

#### Power

Power Source	AC Adapter Included
Output Voltage	9V DC
Output Current	0.3A



Center Tip Polarity      Positive

Power Consumption (In Watts)      2.7

---

#### Physical Characteristics

Color	Black
Material	Steel
Product Length	5.1 in [13.0 cm]
Product Width	2.2 in [56.0 mm]
Product Height	7.7 in [19.5 cm]
Weight of Product	14.8 oz [419.0 g]

---

#### Packaging Information

Package Length	6.1 in [15.6 cm]
Package Width	7.2 in [18.2 cm]
Package Height	3.4 in [87.0 mm]
Shipping (Package) Weight	25.8 oz [732.0 g]

---

#### What's in the Box

Included in Package	2 Port VGA Auto Switch
	Universal Power Adapter (US/UK/EU/AUS)
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

