Product specifications

Eaton TEN-100K-6

Catalog Number: TEN-100K-6

Eaton Power-Sure 700 TEN power conditioner, 11833 BTU/h, Three-phase, 97% typical, 95% minimum, 480Y/277V

General specifications

Product Name	Catalog Number
Eaton Power-Sure 700 power conditioner	TEN-100K-6

UPC	Product Length/Depth
743172023131	35.5 in

Product Height	Product Width
76 in	34.4 in

Product Weight	Warranty
1660 lb	1 year

Certifications

FCC Cat. A ANSI/IEEE Std C62.41 CSA Certified UL 1012

Product specifications

Type

Transformer

Phase

Three-phase

Bypass

Bypass

Efficiency

97% typical, 95% minimum

Output

Hardwired

Model

Metering

Operating Temperature

-10° to 40°C

Topology

Line conditioner

BTU rating

11833 BTU/h

Output voltage

480Y/277V

Indicators

Reg volt (3 green on phase), over temp cond (red)

Resources

Brochures

Power-Sure 700 - Product Assist

Installation instructions

Power-Sure 700 - Instruction Manual

Specifications and datasheets

Power-Sure 700 - Technical Data

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia