

## 25 ft DVI-D Dual Link Cable - M/M

**Product ID:** DVIDDMM25



The DVIDDMM25 25ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 25 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 25 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Industry Standards	DVI DDWG Standard

---

#### Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	25.0 ft [7.6 m]
Product Length	25.0 ft [7.6 m]
Weight of Product	26.9 oz [763 g]

---

#### Packaging Information

Package Length	9.4 in [23.8 cm]
Package Width	2.2 in [56 mm]
Package Height	11.8 in [30 cm]
Shipping (Package) Weight	26.9 oz [763 g]

---

#### What's in the Box



Included in Package      25 ft DVI-D Dual Link Cable - M/M

---

***\*Product appearance and specifications are subject to change without notice.***

