

2 Port VGA Video Splitter with Audio - USB Powered

Product ID: ST122LEA



The ST122LEA 2 Port VGA Video Splitter with Audio and USB power is our most compact VGA splitter, allowing a computer to simultaneously display VGA video on two monitors from a single source.

Support for resolutions up to 2048x1536 resolution and stereo audio makes this device perfect for classrooms, trade shows, or any environment requiring high quality video on several displays.

This VGA splitter is able to draw power from your source PC or media player using an available USB port, instead of using a conventional power adapter making it easy to install where power outlets are not available. The splitter also features a built-in booster circuit that allows you to locate VGA monitors up to 200ft away from your system.

Backed by a StarTech.com 2-year warranty and FREE lifetime tech support.

Certifications, Reports and Compatibility

Applications

- Ideal for small digital signage installations with minimal space or power outlets - simply plug into a USB port
- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Features

- Compact, space-saving design
- Includes USB power cord
- 300 MHz bandwidth for high bandwidth fast moving video
- Provides brilliant resolutions up to 2048 x 1536 60 Hz
- Supports stereo audio using 3.5mm audio jacks
- Maximum distances up to 65 meters (210 feet)

Hardware

Warranty	2 Years
Ports	2
AV Input	VGA
AV Output	VGA
Cabling	Cat 5 UTP or better
Audio	Yes
Industry Standards	DDC, DDC2, DDC2B, on Video Out Port 1

Performance

Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	2048x1536
Wide Screen Supported	Yes

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub) 3.5 mm Mini-Jack (3 Position)
Connector B	VGA (15 pin, High Density D-Sub) 3.5 mm Mini-Jack (3 Position)

Indicators

LED Indicators Green - Power

Power

Power Source	USB-Powered
Output Voltage	5 DC
Output Current	0.5A

Environmental

Operating Temperature	0C to 70C (32C to 158C)
Storage Temperature	-20C to 85C (-4C to 185C)
Humidity	0~95% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	2.7 in [68.0 mm]
Product Width	2.1 in [53.0 mm]
Product Height	0.9 in [23.0 mm]
Weight of Product	3.9 oz [111.0 g]

Packaging Information

Package Length	5.7 in [14.5 cm]
Package Width	8.3 in [21.0 cm]
Package Height	1.9 in [47.0 mm]
Shipping (Package) Weight	8.7 oz [246.0 g]

What's in the Box

Included in Package	Video Splitter
	USB to DC power cable
	User Manual

**Product appearance and specifications are subject to change without notice.*

