

4 Port DVI Video Splitter with Audio

Product ID: ST124DVIA



The ST124DVIA DVI splitter lets you share one DVI video and audio source on four displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source.

With support for high definition resolutions up to 1080p (HDTV)/1920x1200 (PC), the DVI splitter delivers a simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments).

The DVI video splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

This product is TAA compliant and backed by StarTech.com's 2-year warranty with FREE lifetime tech support.

Certifications, Reports and Compatibility

Applications

- Connect DVI projectors, monitors, large displays, and wall display systems for digital signage applications and ensuring content is delivered to target audience.
- Great for use in tradeshows, POS retail, healthcare, transportation terminals, education, house of worship.

Features

- Supports resolutions of up to 1920 x 1200 pixels @ 60 Hz
- Split both video and 3.5mm analog stereo audio

- DVI, and HDCP compliant for easier HD video distribution
- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion
- Easy setup for a quick connection in minutes

Hardware

Warranty	2 Years
AV Input	DVI
Ports	4
AV Output	DVI
Cabling	DVI

Performance

Max Distance	10 m / 33 ft
Maximum Digital Resolutions	1920x1200 @ 60Hz
Wide Screen Supported	Yes

Connector(s)

Connector A	DVI-I (29 pin)
	3.5 mm Mini-Jack (3 Position)
Connector B	DVI-I (29 pin)
	3.5 mm Mini-Jack (3 Position)

Indicators

LED Indicators	Green - Power/Link
	Green - Link

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	9V DC
Output Current	0.6A



Center Tip Polarity Positive

Power Consumption (In Watts) 5.4

Environmental

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 0~80% RH

Physical Characteristics

Color Black

Material Aluminum

Product Length 8.7 in [22 cm]

Product Width 5.3 in [13.5 cm]

Product Height 1.7 in [44 mm]

Weight of Product 2.4 lb [1.1 kg]

Packaging Information

Package Length 15.7 in [40 cm]

Package Width 3.5 in [88 mm]

Package Height 8.4 in [21.3 cm]

Shipping (Package) Weight 4.2 lb [1.9 kg]

What's in the Box

Included in Package

- 4-port DVI splitter
- rack mounts
- screw kit
- rubber feet
- universal power adapter (US, UK, EU, ANZ)

instruction manual

****Product appearance and specifications are subject to change without notice.***

