



Just plug-and-play for hard drive enclosures, printers, modems, cameras, and other SuperSpeed USB peripherals. This cable provides a transfer rate of up to 4.8 Gbps when connected with a USB 3.0 compliant host and device. Foil and braid shielding reduces EMI/RFI interference and twisted pair construction helps reduce crosstalk thus ensuring SuperSpeed, error-free data transfer. Protective overmolded connector is color-coded blue to highlight USB 3.0 connectivity compatibility.

[B]Please Note:[/B] USB 3.0 (4.8 Gbps) provides TEN TIMES the capability of USB 2.0 (480 Mbps); it also provides up to 900 mA power instead of the 500 mA available with USB 2.0. Type A connections are backwards compatible to USB 2.0 and even USB 1.1. Finally, while USB 2.0 cables will work with USB 3.0 devices (at the lower USB 2.0 transmission speed and power), you won't enjoy the SuperSpeed of USB 3.0 without connecting with USB 3.0 cables!

## Features & Benefits

- Carries USB 3.0 data signals and power
- Up to 4.8 Gbps bandwidth
- Shielded to protect from interference

## Specifications

### General Info

Product Line	C2G	UPC Number	757120541721
Country Of Origin	VietNam	Application Sector	Residential, Commercial
Warranty Type	Lifetime	Type	Cable

### Dimensions

Cable Length	9.8 ft
--------------	--------

### Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

### Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	28 AWG
Cable Type	USB	Data Transfer Rate	480 Mbps
Adapter Rear	USB 3.0 A Male	Adapter Front	USB 3.0 A Male