



Just plug-and-play for hard drive enclosures, printers, modems, cameras, and other SuperSpeed USB peripherals. This cable provides a transfer rate of up to 4.8 Gbps when connected with a USB 3.0 compliant host and device. Foil and braid shielding reduces EMI/RFI interference and twisted pair construction helps reduce crosstalk thus ensuring SuperSpeed, error-free data transfer. Protective overmolded connector is color-coded blue to highlight USB 3.0 connectivity compatibility.

Please Note: USB 3.0 (4.8 Gbps) provides TEN TIMES the capability of USB 2.0 (480 Mbps); it also provides up to 900 mA power instead of the 500 mA available with USB 2.0. Type A connections are backwards compatible to USB 2.0 and even USB 1.1. Finally, while USB 2.0 cables will work with USB 3.0 devices (at the lower USB 2.0 transmission speed and power), you won't enjoy the SuperSpeed of USB 3.0 without connecting with USB 3.0 cables!

Features & Benefits

Carries USB 3.0 data signals and power

Up to 4.8 Gbps bandwidth

Shielded to protect from interference

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120541769	Country Of Origin	Vietnam
Application Sector	Commercial, Residential	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	3.3 FT	Cable Length	3.3 ft
-------------------	--------	--------------	--------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Cable Type	USB
Amperage	900 mA	Data Transfer Rate	480 Mbps

Adapter Rear	USB 3.0 Micro-B Male	Adapter Front	USB 3.0 A Male
--------------	----------------------	---------------	----------------
