

Dual Monitor USB 3.0 Docking Station with HDMI - DVI - 6 x USB Ports

Product ID: USB3SDOCKHD



This USB 3.0 dock combines a 6 port USB 2.0/USB 3.0 hub, headphone and microphone audio connectors, and a Gigabit Ethernet RJ45 port into a single docking station.

Offering flexible dual video combinations right out-of-the-box, this universal laptop docking station features HDMI and DVI external monitor output providing up to 1920x1200p resolutions, as well as an included DVI to VGA adapter for added flexibility.

The built-in USB hub features 2 USB 3.0 ports and 4 USB 2.0 ports for connecting extra peripherals such as external hard drives or a wired mouse as if they connected directly to your laptop.

With an upright design, the dock occupies as little desk space as your smart phone, so it's perfect for hoteling or hot desk environments.

The integrated RJ45 Ethernet port supports speeds of 10/100/1000 Mbps, giving you an instant connection to a reliable wired network.

StarTech.com's laptop docking stations can be used for cost savings and faster deployment with just a single cable. This USB 3.0 Docking Station is backed by a competitive 3-year warranty and free lifetime multilingual Technical Support.

Certifications, Reports and Compatibility

Applications

- Shared workspaces
- Hot/Remote desks

- Convert laptop to desktop workstation

Features

- Connect dual monitors (HDMI and DVI) to your Mac or Windows laptop
- Achieve sharp resolution with 1920 x 1200p on dual displays
- Connect more devices with 6 USB ports - 2 x USB 3.0 and 4 x USB 2.0
- Setup your workstation anywhere and save space with the mobile upright design
- Connect to the networks with the built in 10/100/1000 Mbps compatible RJ45 Ethernet port

Hardware

Warranty	3 Years
4K Support	No
Fast-Charge Port(s)	No
Displays Supported	2
Bus Type	USB 3.0
Industry Standards	IEEE 802.3, 802.3u, and 802.3ab
Chipset ID	DisplayLink - DL-3900 VIA/VLI - VL810 Terminus - FE1.1 Realtek - RTL8211E

Performance

Maximum Digital Resolutions	1920 x 1200 Lower resolutions are also supported.
Type and Rate	USB 3.0 - 5 Gbit/s USB 2.0 - 480 Mbit/s
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes



Connector(s)

Connector Type(s)	USB Type-B (9 pin) USB 3.0
	DVI-I (29 pin)
	USB Type-A (4 pin) USB 2.0
	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	3.5 mm Mini-Jack (3 Position)
	RJ-45
	HDMI (19 pin)

Software

OS Compatibility	Windows XP SP3 (32-bit), Vista, 7, 8, 8.1, 10 macOS 10.6 - 10.12, 10.14 - 10.15, 11.0 Chrome OS v55+
------------------	--

Special Notes / Requirements

System and Cable Requirements	CPU: i3 Dual core 2.8GHz or better, RAM: 2GB or higher, Available USB 3.0 port
Note	The DVI-I connector supports DVI-I signaling (digital and analog)

Indicators

LED Indicators	Power (Blue) USB Hub Link (Blue)
----------------	-------------------------------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.8A
Output Voltage	5 DC
Output Current	4A
Plug Type	C
Power Consumption (In Watts)	20



Environmental

Operating Temperature	10C to 40C (50F to 104F)
Storage Temperature	-10C to 80C (14F to 176F)

Physical Characteristics

Color	Black
Material	Plastic
Product Length	4.9 in [12.5 cm]
Product Width	2.8 in [70.0 mm]
Product Height	7.7 in [19.5 cm]
Weight of Product	13.1 oz [370.0 g]

Packaging Information

Package Quantity	1
Package Length	10.7 in [27.3 cm]
Package Width	7.5 in [19.0 cm]
Package Height	4.3 in [10.9 cm]
Shipping (Package) Weight	33.4 oz [947.0 g]

What's in the Box

Included in Package	USB 3.0 Docking Station
	3.3 ft [1 m] USB 3.0 Cable
	DVI to VGA Adapter
	Universal Power Adapter (NA/JP, EU, UK, ANZ)
	Instruction Manual

**Product appearance and specifications are subject to change without notice.*

