

6 ft Monitor VGA Cable - HD15 M/M

**Product ID:** MXT101MM



This 6-foot VGA Video Monitor Cable features two HDB15 (male) connectors, providing a reliable VGA connection.

For best performance, this VGA extension cable is designed to be used with low-resolution applications. For applications that require higher resolutions, see our 6ft Coax VGA Cable (MXT101MMHQ).

MXT101MM is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

### Features

- Supports low resolution applications
- Guaranteed reliability

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel

Cable Jacket Material PVC - Polyvinyl Chloride

Cable Shield Material Aluminum-Mylar Foil with Braid

---

**Connector(s)**

Connector A VGA (15 pin, High Density D-Sub)

Connector B VGA (15 pin, High Density D-Sub)

---

**Special Notes / Requirements**

Note Pin number 9 is not populated on these connectors

---

**Physical Characteristics**

Color Gray

Wire Gauge 28 AWG

Cable Length 6.0 ft [1.8 m]

Product Length 6.0 ft [1.8 m]

Product Width 1.3 in [33 mm]

Product Height 0.7 in [18 mm]

Weight of Product 4.3 oz [122 g]

---

**Packaging Information**

Package Length 8.9 in [22.5 cm]

Package Width 4.9 in [12.5 cm]

Package Height 0.5 in [13 mm]

Shipping (Package) Weight 4.5 oz [127 g]

---

**What's in the Box**

Included in Package 6 ft VGA Monitor Cable - HD15 M/M

---

*\*Product appearance and specifications are subject to change without notice.*