

3 ft 14 AWG Computer Power Cord - IEC C14 to IEC C15

Product ID: PXTC14C153



The PXTC14C153 C14 to C15 Power Cord (3 ft) features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to C14 Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this C14 to C15 power cable is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect large server applications to PDUs located in high-temperature environments
- Compatible with Cisco, HP and other hardware devices with C15 power connections

Features

- 1x IEC 60320 C15 connector
- 1x IEC 60320 C14 connector
- Rated to carry 250V at 15A
- 14 AWG wire
- UL, RoHS Compliant

- Fully molded strain relief connectors
- Temperature Rating of 105C

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	IEC 60320 C14 Power
Connector B	IEC 60320 C15 Power

Power

Input Voltage	250 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]
Product Width	1.1 in [28.5 mm]
Product Height	0.8 in [20.5 mm]
Weight of Product	6.4 oz [181 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]



Package Height	2.4 in [62 mm]
Shipping (Package) Weight	6.6 oz [186 g]

What's in the Box

Included in Package	3ft Computer Power Cord 14 AWG - C14 to C15
---------------------	---

****Product appearance and specifications are subject to change without notice.***

