

6 ft 14 AWG Computer Power Cord - IEC C14 to IEC C15

**Product ID:** PXTC14C156



The PXTC14C156 C14 to C15 Power Cord (6 ft) features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to C14 Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this C14 to C15 power cable is backed by our Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Connect large server applications to PDUs located in high-temperature environments
- Compatible with Cisco, HP and other hardware devices with C15 power connections

### Features

- 1x IEC 60320 C15 connector
- 1x IEC 60320 C14 connector
- Rated to carry 250V at 15A
- 14 AWG wire
- UL, RoHS Compliant

- Fully molded strain relief connectors
- Temperature Rating of 105C

---

#### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

---

#### Connector(s)

Connector A	IEC 60320 C14 Power
Connector B	IEC 60320 C15 Power

---

#### Power

Input Voltage	250 AC
Input Current	15 A

---

#### Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.1 in [28.5 mm]
Product Height	0.8 in [20.5 mm]
Weight of Product	11.0 oz [312 g]

---

#### Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]



Package Height 2.0 in [50 mm]

Shipping (Package) Weight 11.2 oz [317 g]

---

**What's in the Box**

Included in Package 6ft Computer Power Cord 14 AWG - C14 to C15

---

***\*Product appearance and specifications are subject to change without notice.***

