

20m / 65 ft Active USB 2.0 A to B Cable - M/M

Product ID: USB2HAB65AC



The USB2HAB65AC 65ft/20m USB A to B cable incorporates bus-powered active circuitry, which enables it to perform beyond the 5-meter limit of a standard USB cable.

The longer connection provides enough cable length to connect your USB 2.0 peripherals up to 20m away from your PC, Laptop or Server, allowing you to position your devices as needed.

This active USB 2.0 cable is designed with top quality materials for high durability, and is backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Connect a USB Type B peripheral (hard drive enclosure, printer, keyboard, mouse, modem, etc.) up to 65ft away from your PC, Laptop or Server – beyond the USB 2.0 5-meter limitation

Features

- 1x USB 'A' male connector
- 1x USB 'B' male connector
- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered, no external power source required

- Aluminum-Mylar Foil with Braided Shielding
- Compatible with PC Windows 8/7/Vista/XP and Mac computer systems

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	USB B (4 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	65.0 ft [19.8 m]
Product Length	65.0 ft [19.8 m]
Weight of Product	28.5 oz [807 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.6 cm]
Package Width	8.4 in [21.4 cm]
Package Height	2.3 in [59 mm]
Shipping (Package) Weight	34.2 oz [968 g]



**What's in the
Box**

Included in Package	20m (65 ft) Active USB 2.0 A to B Cable - M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***

