




C2G
12ft (3.7m) Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable - Red
Part No. CG-04003



For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

Features & Benefits

- Snagless design protects clips when plugging and unplugging
- Standard RJ45 connectors and unshielded twisted pair wires
- Available in 10 colors to color-code a network
- Available in lengths up to 150ft

Specifications

General Info

Product Line	C2G	Color	Red
UPC Number	757120040033	Country Of Origin	Vietnam
Features	PoE (Power Over Ethernet)	Application Sector	Residential, Commercial, Industrial
Warranty Type	Lifetime	Type	Cable

Dimensions

Product Length US	12.0 FT	Cable Length	12 ft
-------------------	---------	--------------	-------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Cable Type	Ethernet Patch Cable, Booted, Snagless, Unshielded (UTP)	Jacket Rating	Standard / Non-Rated
Adapter Rear	RJ-45 Male	Adapter Front	RJ-45 Male