



C2G

**20ft (6.1m) Cat6 Non-Booted Unshielded (UTP) Ethernet Network Patch Cable - Blue**

Part No. CG-04098



For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code your network installation.

## Features & Benefits

Designed for network adapters, hubs, switches, routers, HDBaseT applications and more

Meets all Cat6 TIA/EIA requirements for supporting a wide variety of applications

Available in a variety of colors to color-code a network

Supports 10 Gigabit networks up to 180ft for fast data transmission and maximum performance and supports 1 Gigabit up to 328ft

Constructed with unshielded twisted pair (UTP) wires, designed to counter EMI, RFI, and crosstalk

## Specifications

### General Info

Product Line	C2G	Color	Blue
UPC Number	757120040989	Country Of Origin	Vietnam
Features	PoE (Power Over Ethernet)	Application Sector	Commercial, Industrial, Residential
Warranty Type	Lifetime	Type	Cable

### Dimensions

Product Length US	20.0 FT	Cable Length	20 ft
-------------------	---------	--------------	-------

### Listing Agencies / 3rd Party Agencies

CE Certified	Yes	REACH Compliant	Yes
--------------	-----	-----------------	-----

---

## Additional Information

---

RoHS Conformant    Yes

---

## Technical Information

---

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Cable Type	Ethernet Patch Cable, Unbooted, Unshielded (UTP)	Jacket Rating	Standard / Non-Rated
Cable Diameter	6 mm	Adapter Rear	RJ-45 Male
Adapter Front	RJ-45 Male		

---