



**C2G**  
**2ft (0.6m) Cat5e Snagless Unshielded (UTP) Ethernet Network Patch Cable - White**  
Part No. CG-00482



For fast Ethernet networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat5e TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

## Features & Benefits

|                                                             |                                                            |
|-------------------------------------------------------------|------------------------------------------------------------|
| Snagless design protects clips when plugging and unplugging | Standard RJ45 connectors and unshielded twisted pair wires |
| Available in 10 colors to color-code a network              | Available in lengths up to 150ft                           |

## Specifications

### General Info

|                    |                                     |                   |          |
|--------------------|-------------------------------------|-------------------|----------|
| Product Line       | C2G                                 | Color             | White    |
| UPC Number         | 757120004820                        | Country Of Origin | Vietnam  |
| Application Sector | Commercial, Industrial, Residential | Warranty Type     | Lifetime |
| Type               | Cable                               |                   |          |

### Dimensions

|                   |        |              |      |
|-------------------|--------|--------------|------|
| Product Length US | 2.0 FT | Cable Length | 2 ft |
|-------------------|--------|--------------|------|

### Listing Agencies / 3rd Party Agencies

|              |     |                 |     |
|--------------|-----|-----------------|-----|
| CE Certified | Yes | REACH Compliant | Yes |
|--------------|-----|-----------------|-----|

### Additional Information

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

### Technical Information

|                 |                                                          |               |                      |
|-----------------|----------------------------------------------------------|---------------|----------------------|
| Jacket Material | PVC (Polyvinyl Chloride)                                 | Wire Gauge    | 24 AWG               |
| Cable Type      | Booted, Ethernet Patch Cable, Snagless, Unshielded (UTP) | Jacket Rating | Standard / Non-Rated |
| Cable Diameter  | 5.3 mm                                                   | Adapter Rear  | RJ-45 Male           |
| Adapter Front   | RJ-45 Male                                               |               |                      |