

6 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Product ID: DVIIDMM6



The DVIIDMM6 6ft DVI-I Dual Link cable features 2 male DVI-I (29-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 6ft DVI-I male to male cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-I Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards
- Supports both analog and digital displays

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

Performance

Maximum Data Transfer Rate	9.9 Gbits/sec
----------------------------	---------------

Connector(s)

Connector A	DVI-I (29 pin)
Connector B	DVI-I (29 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	10.9 oz [308 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.4 in [35 mm]
Shipping (Package) Weight	11.2 oz [318 g]



**What's in the
Box**

Included in Package 6 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

****Product appearance and specifications are subject to change without notice.***

