

## 6 ft DVI-I Dual Link Digital Analog Monitor Extension Cable M/F

**Product ID:** DVIIDMF6



The DVIIDMF6 DVI-I Dual-Link Digital Analog Monitor Extension Cable allows you to extend the connection distance between your DVI-I devices by up to 6-feet.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-I Dual Link display or projector by up to 6ft

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot plugging of DVI display devices

- Compliant with DVI DDWG Standards
- Supports both analog and digital displays

---

#### Hardware

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

---

#### Performance

Maximum Data Transfer Rate	9.9 Gbits/sec
----------------------------	---------------

---

#### Connector(s)

Connector A	DVI-I (29 pin)
Connector B	DVI-I (29 pin)

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	9.7 oz [276.0 g]

---

#### Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	10.1 oz [285.0 g]

---

#### What's in the Box

Included in Package

6 ft Dual Link Digital Analog DVI-I Extension Cable - M/F

---

***\*Product appearance and specifications are subject to change without notice.***

