

4 ft Heavy Duty 14 AWG Computer Power Cord - NEMA5-15P to C15

**Product ID:** PXT515C154



The PXT515C154 4-foot Computer Power Cord features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to NEMA 5-15P Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this 5-15P to C15 power cable is backed by our Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Compatible with Cisco, HP and other hardware devices with C15 power connections
- Connect large servers to PDUs, even in high-temperature environments

### Features

- 1x NEMA 5-15 Plug
- 1x IEC 60320 C15 connector
- Rated to carry 125V at 15A
- 14 AWG wire
- UL, RoHS compliant

- Fully molded strain relief connectors
- Temperature Rating of 105C

---

#### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

---

#### Connector(s)

Connector A	NEMA 5-15 Power (North America)
Connector B	IEC 60320 C15 Power

---

#### Special Notes / Requirements

Note	UL Listed
------	-----------

---

#### Power

Input Voltage	125 AC
Input Current	15 A

---

#### Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	4.0 ft [1.2 m]
Product Length	4.0 ft [1.2 m]
Weight of Product	8.0 oz [226 g]

---

#### Packaging Information

Package Quantity	1
Package Length	11.4 in [29 cm]
Package Width	5.7 in [14.5 cm]



Package Height 0.9 in [22 mm]

Shipping (Package) Weight 8.0 oz [227 g]

---

**What's in the Box**

Included in Package 4 ft Heavy Duty Computer Power Cord - NEMA5-15P to C15

---

***\*Product appearance and specifications are subject to change without notice.***

