



C2G
6ft (1.8m) Cat6a Snagless Shielded (STP) Ethernet Network Patch Cable - Black
Part No. CG-00711



This Snagless Shielded Cat6a patch cable is ideal for use with 10GBase-T ports and equipment, such as network adapters, hubs, switches, routers, DSL/cable modems and patch panels, and will protect a high speed 10 Gigabit network connection from noise and electromagnetic interference. For voice/data/video distribution, this cable will handle bandwidth-intensive applications and drastically reduces both impedance and structural return loss (SRL). Each patch cable is fully tested to meet ANSI/TIA 568 C.2 Cat6a component requirements.

Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality cable and plugs, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code a network installation. Individual length label on each cable for ease of use.

Features & Benefits

- Designed for network adapters, hubs, switches, routers, HDBaseT applications and more
- Supports 10 Gigabit networks up to 328ft for fast data transmission and maximum performance
- Meets the ANSI/TIA-568-C.2 Cat6a requirements for supporting a wide variety of applications
- Constructed with shielded twisted pair (STP) wires, designed to protect a high speed network from noise and electromagnetic interference
- Snagless connector design for high density environments and protecting the RJ-45 connector's lock
- Available in a variety of colors to color-code a network

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120007111	Country Of Origin	VietNam
Application Sector	Residential, Commercial, Industrial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Cable Length	6 ft
--------------	------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	26 AWG
Cable Type	Snagless, Shielded (STP), Ethernet Patch Cable	Jacket Rating	Standard Non-Rated
Adapter Rear	RJ-45 Male	Adapter Front	RJ-45 Male
