




NOTE:

1.CABLE:1354(S)28#*3C+24#*9C+AEB 85% COLOR:BLACK OD:0.34" (W12090101)

MARKING:BLACK BOX CORPORATION GUARANTEED FOR LIFE (724)

746-5500 E223179(UL)TYPE CL2 3C/28AWG AND 9C/24AWG 75°C

2.CONNECTOR: HDD15M BLUE INSULATOR NICKEL SHELL

3.THUMBSCREW: 4-40UNC HD 0.32"*1.97" K001(BLACK)

4.FERRITE CORE:0.69"*1.12"*0.38"

5.PVC: BLACK(V398) 45P

6.LABEL:P/N LABEL

7.COVER: DUST COVERHDD15PTRANSPANRENCE.

8.LABEL: YEAR/MONTH LABEL

ELECTRONIC TEST:

A.OPEN/SHORT/INTERMITTENCE: 100%.

B.HI-POT: 300V DC/sec

C.INSULATION RESISTANCE: 20M ohm (MIN)

D.CONDUCTIVE RESISTANCE: 0<L≤10FT 2 ohm (MAX)

10FT≤L<15FT 3 ohm (MAX)

15FT≤L<30FT 4 ohm (MAX)

30FT≤L<100FT 6 ohm (MAX)

L>100FT 10 ohm (MAX)

E.CPK Measure point Y1-Y7.

CN1	PIN	OUT	CN2
1	RED	COAX	1
2	GREEN	COAX	2
3	BLUE	COAX	3
4	BLACK		4
5	BROWN		5
6	RED	Spiral	6
7	GREEN	Spiral	7
8	BLUE	Spiral	8
9	YELLOW		9
10	ORANGE		10
11	GREEN		11
12	VIOLET		12
13	RED		13
14	BLUE		14
15	GRAY		15
SHELL	BRAID		SHELL

EVNPS06B-0003-MM	3FT+3"/-0	3FT
EVNPS06B-0005-MM	5FT+3"/-0	5FT
EVNPS06B-0010-MM	10FT+6"/-0	10FT
EVNPS06B-0020-MM	20FT+6"/-0	20FT
EVNPS06B-0025-MM	30FT+6"/-0	25FT
EVNPS06B-0050-MM	50FT+6"/-0	50FT
EVNPS06B-0075-MM	75FT+6"/-0	75FT
EVNPS06B-0100-MM	100FT+1FT/-0	100FT

BLACK BOX®			
Tolerance:	Approved by:		
X. ±	wayne		
.X ±	Checked by:	BLACK BOX P/N:	
.XX ±	lucency	EVNPS06B-xxxx-MM	
.XXX ±	Drawn by:	Description:	
Angle:	xiong	HDD15M TO HDD15M CABLE	
X' ±	Date:	DWG. NO:	
.X' ±	11.12.24		
	Scale:	Unit: mm	
		SHEET:	1 OF 1
		REV:	01

01	CHANGE YEAR MONTH LABEL PRESS	xiong	11.12.24
REV	ECN NO	DESCRIPTION	Drawn DATE