

4 Port USB 3.0 Hub plus 3 Dedicated USB Charging Ports (2 x 1A & 1 x 2A) - Wall Mountable Metal Enclosure

Product ID: ST4300U3C3



The ST4300U3C3 USB 3.0 Hub enables simultaneous data hub and USB charging functionality by adding three dedicated USB charge ports, as well as four USB 3.0 data ports, for a total of seven ports, all through a single USB 3.0 host connection.

The USB hub ports are compliant with the SuperSpeed USB 3.0 specification, offering data transfer rates up to 5 Gbps, and are backward compatible with USB 2.0 and 1.x specifications.

This externally powered USB hub also integrates 3 dedicated USB charging ports, providing 2 x 1A and 1 x 2A ports, enabling both data hub and USB charging station functionality. Support for USB Battery Charging Specification 1.2 lets you charge most mobile devices, including the Apple iPhone, iPad, Microsoft Surface, Samsung Galaxy Tab and more.

Designed for easy access to the ports when connecting or disconnecting devices, the hub features an upright port orientation, in a compact and durable metal enclosure. For added flexibility, the hub includes a bracket for wall-mounted installations.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Use in IT helpdesk or tech bench environments to provide USB hub and charge ports for multiple devices
- Installation in locations where USB 3.0 ports need to be securely mounted to a surface, such as a wall or under a desk

- Expand your USB 3.0 capabilities at home or in the office

Features

- Provides 4 USB 3.0 hub ports, and 3 dedicated USB charging ports (2 x 1A, 1 x 2A)
- Supports USB Battery Charging Specification 1.2, including Apple and Samsung Galaxy devices
- Compliant with SuperSpeed USB 3.0, with support for up to 5 Gbps
- Backward compatible with USB 2.0 and 1.x devices
- Compact, metal enclosure
- Includes wall-mount bracket

Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	Yes
Ports	7
Bus Type	USB 3.0
Industry Standards	USB Battery Charging Specification Rev. 1.2
Chipset ID	VIA/VLI - VL812

Performance

Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s

Connector(s)

Connector Type(s)	USB Type-B (9 pin) USB 3.0
	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	USB Type-A (4 pin) USB 2.0

Software



OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Special Notes / Requirements

System and Cable Requirements	Available USB 3.0 port
Note	If connected to a USB 2.0 host port, performance may be limited

Indicators

LED Indicators	Power Hub Port Connection LEDs
----------------	-----------------------------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.3 A
Output Voltage	12V DC
Output Current	3 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	36

Environmental

Operating Temperature	5C to 35C (41F to 95F)
Storage Temperature	-20C to 50C (-4F to 122F)
Humidity	20~80% RH

Physical Characteristics

Color	Black
Form Factor	Desktop
Material	Aluminum
Product Length	4.3 in [11.0 cm]



Product Width	1.8 in [45.0 mm]
Product Height	0.9 in [24.0 mm]
Weight of Product	4.6 oz [131.0 g]

Packaging Information

Package Length	4.1 in [10.4 cm]
Package Width	6.5 in [16.6 cm]
Package Height	3.5 in [90.0 mm]
Shipping (Package) Weight	21.4 oz [606.0 g]

What's in the Box

Included in Package	USB Charging Hub
	USB 3.0 Cable
	Wall Mount Bracket (w/ Screws)
	Rubber Feet
	Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

