



This adapter converter is an ideal solution for adapting the Mini DisplayPort or Thunderbolt 2 output of a small laptop or tablet so that it may be connected to a monitor which accepts a DVI-D input. This adapter converter carries a digital video signal, supports up to a 1920x1200 resolution and meets the requirements of high performance applications. This adapter converter is a perfect accessory for Microsoft® Surface® products and other leading laptops.

Discover more connectivity solutions for the [Microsoft Surface](#)

Features & Benefits

Adapts a Mini DisplayPort/Thunderbolt 2 output to Single-Link DVI-D

Carries a digital video signal

Supports up to a 1920x1200 resolution

Use with a DVI-D cable for a complete solution

Compatible with the Microsoft® Surface® Pro 6, Surface Laptop 2, and other leading laptops

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120543114	Country Of Origin	China
Compliance	CE	Application Sector	Commercial, Residential
Warranty Type	5-Year	Type	Active Device, Adapter, Converter

Dimensions

Product Length US	8.0 in	Cable Length	0.67 ft
-------------------	--------	--------------	---------

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	32 AWG
Video Resolution	1080p, WUXGA (1920x1200)	Bend Radius	51 mm
Number of Ports	1	Jacket Rating	Standard / Non-Rated
Cable Diameter	5.2 mm	Data Transfer Rate	18 Gbps
Connector 2	DVI-D Single Link Female	Connector 1	Mini DisplayPort Male
Video Output Support	DVI-D	Operating Temperature	0°-50°C
Video Input Support	Mini DisplayPort	Voltage	30.0 V
Active/Passive	Active	Storage Temperature	-25° - 70° C