

12U Rack Enclosure Server Cabinet - 21 in. Deep - Wood Finish - Flat Pack

Product ID: RKWOODCAB12



The RKWOODCAB12 12U Office Server Cabinet lets you store your server, network or AV equipment discreetly in the office, with a stylish wood finish. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Designed to blend in with your office or boardroom furniture, this 12U server cabinet features wood laminate exterior panels with a shaded glass front window that keeps your equipment visible for monitoring, as well as front and rear key-locks to prevent unauthorized access. To help keep your valuable equipment running cooler, we've included a ventilation panel to maximize airflow. The cabinet also features durable casters, so that positioning your server equipment as needed isn't a hassle.

The 4-post enclosed rack supports a weight capacity of up to 300lbs (136kg) and offers rails with adjustable mounting depth from 17in (423mm) to 21in (523mm) to accommodate various sizes of equipment. Making it easy to route your cables where you need them, the 12U cabinet offers cable grommets on the rear and top panels, and a cable entry panel at the base.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount server or networking equipment in a well-furnished boardroom
- Add an attractive server cabinet that won't be an eyesore in small / home-office areas with limited space

Features

- 12U Enclosed cabinet with a stylish wood finish
- Supports a weight capacity of up to 300lbs (136kg)
- TAA compliant for GSA Schedule purchases
- Adjustable mounting depth from 16.7in (423mm) to 20.6in (523mm)
- Ventilation and cable entry panels
- Casters included
- Front and rear key-lock
- Flat-packed for easy shipping

Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Aluminum
U Height	12U
Special Features	Adjustable Mounting Rails Casters (Included) Easy Assembly Leveling Feet
Mounting Rail Profile	L-Shape
Fan Options	Two Optional Fans: 92 mm
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	300.7 lb [136.1 kg]
------------------------------	---------------------

Physical Characteristics



Color	Black & Brown
Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock with Reversible and Removable Front Door
Side Panel Construction	Wood
Rear Door Construction	Wood
Rear Door Features	Secure Key Lock with Removable Back Door

Product Measurements

Internal Width	20.5 in [52.1 cm]
Internal Depth	25.1 in [63.7 cm]
Product Length	26.0 in [66.0 cm]
Product Width	22.0 in [56.0 cm]
Product Height	25.6 in [65.0 cm]
Weight of Product	67.8 lb [30.7 kg]
Maximum Mounting Depth	20.6 in [52.2 cm]
Minimum Mounting Depth	16.6 in [42.2 cm]
Product Height with Casters	28.4 in [72.1 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	29.6 in [75.3 cm]
Package Width	29.6 in [75.3 cm]
Package Height	1.8 in [46.0 mm]
Shipping (Package) Weight	76.7 lb [34.7 kg]

What's in the Box



Included in Package	Right Side Panel
	Left Side Panel
	Rack Top
	Rack Bottom
	Rear Panel
	Front Door
	Rack Rails
	Front/Rear Support
	Ventilation Panel
	Cable Entry Panel
	Panel Brackets
	Strike Plate
	Round Grommet
	Locking Latches (with 2 keys each)
	Casters
	M6x12 Screws
	M5x12 Screws
	M4x12 Screws
	M6x15
	Cams
	Connecting Bolts
	Dowel Pins
	M5 Screws
	M5 Cage Nuts
	Instruction Manual

**Product appearance and specifications are subject to change without notice.*

