

# CyberPower

## CSP300WUR1 WALL-TAP SURGE PROTECTOR

Protect home and office computers, electronics, and home theater equipment

The Professional Surge Protector CSP300WUR1 safeguards common home and office devices, such as computers and electronics, by absorbing spikes in energy caused by storms and electrical power surges. Designed for convenience, the portable CSP300WUR1 is ideal for travelers. It provides 600 joules of protection, has three surge-protected outlets, and a wall-tap plug. Two USB ports (2.1 Amp shared) charge personal electronics, including smartphones, digital cameras, MP3 players, and other devices.

The CSP300WUR1 also features metal oxide varistor (MOV) technology, an EMI/RFI noise filter, a status indicator, and impact-resistant casing. This surge suppressor comes with a 1-Year Limited Warranty and a Connected Equipment Guarantee.



### TYPICAL APPLICATIONS

- Mobile Devices
- Personal Electronics
- Cell Phones
- Personal Computers

### FEATURES

- Surge suppression: 600 J
- Volts: 125 V
- Plug type: Wall-Tap
- Outlet type: 3 NEMA 5-15R (surge-protected)
- USB-A charge ports: 2
- USB Output: 2.4A (shared)
- EMI/RFI Filtration: Yes
- LED indicator: Yes
- Warranty: 1-Year Limited
- Connected Equipment Guarantee: \$50,000

### SPECIFICATIONS

INPUT	
Input Plug Type	NEMA 5-15P
Maximum Input Current	15 A
Plug Style	Wall-tap
OUTPUT	
Outlet Type	3 - NEMA 5-15R
Outlets - Total	3
USB Charge Port	Yes
USB Charge Port Amperage	2.4 A (Shared)
USB Charge Port Type	2 x Type A
USB Charge Port Voltage	5 VDC

SURGE PROTECTION & FILTERING	
Attenuation	32 dB
Clamping Voltage	400V (H-N, H-G)
EMI/RFI Filtration	Yes
Maximum Surge Current	30,000 A
Maximum Surge Current H-G	15,000 A
Maximum Surge Current H-N	15,000 A
Maximum Surge Voltage	6,000 V
Response Time	<1 Nanosecond
Surge Suppression (Joules)	600 J

CSP300WUR1

WALL-TAP SURGE PROTECTOR

SPECIFICATIONS CONT.

PHYSICAL	
Color	White
Form Factors Supported	Direct Plug
Material of Construction	Plastic
PHYSICAL DIMENSIONS	
Physical Dimensions - Width/Height/Depth (cm)	9.14 x 12.19 x 3.23 cm
Physical Dimensions - Width/Height/Depth (mm)	91 x 122 x 32 mm
Physical Dimensions - Width/Height/Depth (in.)	3.6 x 4.8 x 1.27 in.
Weight (kg)	0.19 kg
Weight (lb)	0.42 lbs.
Country of Origin	China
SHIPPING DIMENSIONS	
Shipping Dimensions - Width/Height/Depth (cm)	15.88 x 5.97 x 9.63 cm
Shipping Dimensions - Width/Height/Depth (mm)	158.75 x 59.69 x 96.27 mm
Shipping Dimensions - Width/Height/Depth (in)	6.25 x 2.35 x 3.79 in.
Weight (kg)	0.23 kg
Weight (lb)	0.50 lbs.

CERTIFICATIONS	
Environmental	RoHS Compliant
Safety	UL1449 3rd Edition
WARRANTY	
CEG Amount	\$50,000
Connected Equipment Guarantee	Lifetime
Product Warranty	1-Year Limited Warranty