



This cable is an ideal solution for connecting the DisplayPort output of a laptop to a computer monitor which accepts a DisplayPort input. This cable carries a digital audio/video signal and the connectors feature latches which secure the cable in the port. Support of a High Bit Rate (HBR) bandwidth means that this cable can carry up to a 8K UHD (7680 x 4320) resolution. This cable meets the requirements of high performance applications.

<

Features & Benefits

Directly connect a DisplayPort output to a DisplayPort input

Carries a digital audio/video signal

Supports a High Bit Rate (HBR) bandwidth and resolutions up to a 8K UHD (7680 x 4320)

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120544029	Country Of Origin	VietNam
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Cable Length	10 ft
--------------	-------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	32 AWG
Video Resolution	8K, 4K 60Hz, 4K 30Hz, 4K, 1080p	Bend Radius	73 mm
Cable Type	Video	Jacket Rating	Standard Non-Rated
Data Transfer Rate	10.8 Gbps	Adapter Rear	DisplayPort Male
Adapter Front	DisplayPort Male	Voltage	30 V