

Travel A/V Adapter: 3-in-1 Mini DisplayPort to VGA DVI or HDMI Converter - White

Product ID: MDP2VGDVHDW



The MDP2VGDVHDW Mini DisplayPort to VGA, DVI or HDMI converter offers a three-in-one solution for connecting an Mini DP video source (such as any of your MacBook or Microsoft Surface Pro devices with mDP) to a VGA, DVI, or HDMI Display. Ensuring compatibility with almost any display, television or projector, this compact and lightweight adapter offers the ideal plug-and-play solution for travel, or BYOD (Bring Your Own Device) applications around the office.

You can walk into any boardroom and be ready to connect, even if you don't know what connection ports are available. The MDP2VGDVHDW maximizes the audio/video connectivity of your MacBook by offering three different output ports, in a single compact adapter.

The three-in-one converter is compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200/1080p you can convert a Mini DisplayPort video source to VGA, HDMI, or DVI without sacrificing video quality.

The Mini DisplayPort converter requires no power adapter and maximizes portability by easily travelling in your laptop bag with a small footprint and lightweight design.

The MDP2VGDVHDW features a sleek white design that looks great next to your MacBook Pro or MacBook Air, and is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Keep the adapter with you while traveling, to connect to virtually any display you come across
- Connect your BYOD laptop/Ultrabook to a provided HDMI, DVI, or VGA display at work

- Connect a DVI, VGA, or HDMI display to your Mini DisplayPort laptop, to use as a secondary monitor

Features

- Three-in-one adapter - mDP to: VGA, DVI, HDMI
- Support for video resolution up to 1920x1200/1080p
- Plug-and-play installation
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal
- Small footprint
- Portable, lightweight construction
- Sleek White Design

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
	Passive
AV Input	Mini DisplayPort - 1.2
AV Output	DVI-D - Single-Link
	HDMI - 1.4
	VGA
Audio	Yes

Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920x1200/1080p
Maximum Digital Resolutions	1920x1200/1080p
Wide Screen Supported	Yes
Audio Specifications	DVI - No Audio Support



HDMI - 7.1 Channel Audio

VGA - No Audio Support

Connector(s)

Connector A	Mini-DisplayPort (20 pin)
Connector B	HDMI (19 pin)
	VGA (15 pin, High Density D-Sub)
	DVI-D (25 pin)

Special Notes / Requirements

Note	<p>Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.</p> <p>The HDMI port is a passive port.</p> <p>The DVI-D is a passive port.</p> <p>The VGA port is an active port.</p> <p>Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling</p>
------	--

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10~85% RH

Physical Characteristics

Color	White
Cable Length	5.9 in [15 cm]
Product Length	10.6 in [27 cm]
Product Width	1.8 in [45 mm]
Product Height	0.6 in [15 mm]
Weight of Product	2.0 oz [57 g]

Packaging Information



Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.8 in [20 mm]
Shipping (Package) Weight	2.3 oz [66 g]

What's in the Box

Included in Package	Mini DisplayPort to HDMI/VGA/DVI Adapter
	Installation Guide

****Product appearance and specifications are subject to change without notice.***

