




REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	2013.10.28
A	CHANGE LABEL	2013.10.31
A	CHANGE THE COLOR INTO BLACK	2013.11.26



MARKING: BLACK BOX CORPORATION GUARANTEED FOR LIFE (724) 746-5500 — GIGABASE CATEGORY 5E — TESTED TO 350MHZ — ▲ E196163-Y CM (UL) c(UL) UTP 60°C 4PR 24AWG STR ▲ ETL VERIFIED TO ANSI/TIA-568-C.2 MM-YY



Conductor	Bare Copper 24AWG 7/0.0077inch approx
Insulation	Thickness:MIN at any point:0.0059inch MAX AVG:0.0098inch Diameter:0.0362inch approx
Jacketing	PVC Thickness:MIN at any point:0.0165inch MAX AVG:0.0189inch Diameter:0.2126inch approx
WIRE	CAT.5E UTP Stranded 24AWGX4P
PLUG	Assembly+BOOT 8P8C 50u"(1.27µm) Gold 1 piece plug
XXX=Length	1ft 2ft 3ft 4ft 5ft 6ft 7ft 10ft 15ft 20ft 25ft 30ft 50ft 100ft

RJ45 Plugs Standard — IEC 60603-7

Attenuation (Maximum):22.5dB @100MHZ ;45.8dB @350MHZ
Cable Type:4-pair UTP
Conductor Gauge:24AWG, stranded
Frequency:Up to 350MHZ
Impedance:100±15 ohms
NEXT (Minimum):35.3dB @100MHZ ;27.1dB @350MHZ
PS-NEXT (Minimum):32.3dB @100MHZ ;24.1dB @350MHZ
Return Loss (Minimum):19dB @100MHZ ;4.56dB @350MHZ
Standards:ANSI/TIA-568-C.2 CAT.5E

orange 2
white/orange
green 3
white/green
blue 1
white/blue
brown 4
white/brown

PINOUT			
PA/R	P1(T568B)	WIRE	P2(T568B)
1	1	WHT/ORG	1
	2	ORG	2
2	3	WHT/GRN	3
	6	GRN	6
3	4	BLU	4
	5	WHT/BLU	5
4	7	WHT/BRN	7
	8	BRN	8

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ±
ANGULAR: MACH ± BEND ±
TWO PLACE DECIMAL ±
THREE PLACE DECIMAL ±

INTERPRET GEOMETRIC
TOLERANCING PER:
MATERIAL
CRS
FINISH
POWDER COAT
DO NOT SCALE DRAWING

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.
©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

BLACK BOX

NAME	DATE	TITLE:
DRAWN	Vinci	2013.11.26
ENG APPR.		
CHECKED		
COMMENTS:		
SIZE PART.NO.		REV
B C5EPC70-BK-XXX		A
SCALE: 1:1		SHEET 1 OF 1