




REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	2013.11.14
A	CHANEG THE COLOR INTO GRAY	2013.11.25
A	CHANEG THE PHYSICAL CHARACTERS	2013.12.04



MARKING: BLACK BOX CORPORATION GUARANTEED FOR LIFE (724) 746-5500 — GIGABASE CATEGORY 5E SHIELDED —TESTED TO 100 MHz — ▲ E196163-Y
CM (UL) α(UL) F/UTP 60°C 4PR 26AWG STR ▲ 3P VERIFIED TO ANSI/TIA-568-C.2 & ISO/IEC 11801 ED.2 & EN 50288-2-2 & IEC 60332-1-2 MM-YY



Conductor	Bare Copper 26AWG 7/0.0060inch approx
Insulation	Thickness:MIN at any point:0.0069inch MAX AVG:0.0098inch Diameter:0.0338inch approx
Jacketing PVC	Thickness:MIN at any point:0.0197inch MAX AVG:0.0217inch Diameter:0.2205inch approx
WIRE	CAT.5E FTP Stranded 26AWGX4P
PLUG	Assembly+BOOT 8P8C 50u"(1.27μm) Gold 1 piece plug
XXX=Length	1ft 2ft 3ft 5ft 6ft 7ft 10ft 15ft 20ft 25ft

RJ45 Plugs Standard – IEC 60603-7

Attenuation (Maximum):22.5dB @100MHZ
Cable Type:4-pair FTP
Conductor Gauge:26AWG, stranded
Frequency:Up to 100MHZ
Impedance:100±15 ohms
NEXT (Minimum):35.3dB @100MHZ
PS-NEXT (Minlimum):32.3dB @100MHZ
Return Loss (Minimum):19dB @100MHZ
Standards:ANSI/TIA-568-C.2 CAT.5E

orange 2 white/orange	green 3 white/green
blue 1 white/blue	brown 4 white/brown

PA/R	PINOUT		
	P1(T568B)	WIRE	P2(T568B)
1	1	WHT/ORG	1
	2	ORG	2
2	3	WHT/GRN	3
	6	GRN	6
3	4	BLU	4
	5	WHT/BLU	5
4	7	WHT/BRN	7
	8	BRN	8

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ±
ANGULAR: MACH ± BEND ±
TWO PLACE DECIMAL ±
THREE PLACE DECIMAL ±

INTERPRET GEOMETRIC
TOLERANCING PER:
MATERIAL CRS
FINISH POWDER COAT
DO NOT SCALE DRAWING

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.
©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

BLACK BOX®

NAME	DATE	TITLE:
Drawn	Vind	2013.11.25
ENG APPR.		
CHECKED		
COMMENTS:		
SIZE PART.NO.		REV
B C5EPC70S-GY-XXX		A
SCALE: 1:1		SHEET 1 OF 1