



GWHD11

Wireless Video Connection Kit for 1 TV with HDMI®

Ditch the cable clutter and embrace wireless freedom with the IOGEAR Wireless Video Connection Kit! This clever kit transmits full HD 1080p video and 5.1 surround sound wirelessly from your HDMI devices to your TV, up to 30ft away. No software or drivers needed - simply plug and play!



HDMI®
HIGH-DEFINITION MULTIMEDIA INTERFACE



Features

- Wireless audio/video kit for one (1) TV with an HDMI connector
- Wireless uncompressed Full HD 1080p audio/video streaming with 3D support up to 30ft*
- Connect and send content from a laptop, game console, Blu-ray player or set-top box/DVR/Cable box
- Supports 5.1 channel digital audio
- Video Resolutions: 480p, 720p, 1080i and 1080p
- No software or driver installation needed
- Based on WHDI™ Technology - Low latency < 1ms; great for wireless gaming
- Add up to 3 additional wireless transmitters (Part# [GWHDSTXB](#)) and expand the number of HDMI devices that can transmit to the receiver**

*Up to 3 additional wireless video transmitters with HDMI connectors, line of site, sold separately - Part# [GWHDSTXB](#)

Requirements

Display:

- HDTV or HD Projector
- HDMI Input

Media Source:

- HDMI Output

*Optional: Additional Wireless Transmitters with HDMI connectors (up to 3 additional units), sold separately - Part# [GWHDSTXB](#)

Package Contents

- 1 x Wireless Transmitter with HDMI Connector
- 1 x Wireless Receiver with HDMI Connector
- 1 x Mini USB to USB Cable
- 2 x USB Power Adapters
- 1 x Remote Control
- 2 x AAA Batteries
- 1 x HDMI Cable
- 1 x Quick Start Guide
- 1 x Warranty Card



Specifications

FUNCTION	GWHD11	DIMENSIONS	GWHD11
Connectors		Unit Dimensions	
Video Input	Transmitter: 1 x HDMI connector (Type A, Male)	Height	Tx: 0.75" (1.9cm), Rx: 1.5" (3.81cm)
Video Output	Receiver: 1 x HDMI connector (Type A, Female)	Length	Tx: 1.12" (2.86cm), Rx: 3.75" (9.52cm)
Power	1 x Mini USB Power Jack (Transmitter and Receiver)	Depth	Tx: 3.12" (7.94cm), Rx: 3.75" (9.52cm)
Video Resolution	480p, 720p, 1080i and 1080p with 3D support	Unit Package Dimensions	
Video Streaming	<1ms Latency	Height	2.50" (6.35 cm)
Audio		Width	9.75" (24.77 cm)
Audio Output	Digital 6Mbps, 2 to 8 channels 16 ~ 24 bits/sec by I2S and S/P DIF bus over WHDI transmission (Dolby Digital & DTS)	Depth	7.38" (18.75cm)
Frequency	5.1 ~ 5.8 GHz (Includes Non-DFS and DFS Frequency Bands)	Master Carton	
Range	Maximum video transmission range is 30ft (10m) in line of site	Height	8" (20.32cm)
LEDs		Width	8" (20.32cm)
Power On	Transmitter: 1 x Blue LED; Receiver: 1 x LED (two-tone: green & red)	Depth	10.25" (26.03cm)
Power		Master Carton Qty.	3
Amps	1A (Transmitter) and 1.5A (Receiver)	Weight	
Voltage	5V DC Mini USB (Transmitter and Receiver)	Master Carton Wt.	5.35lb (2.42kg)
Operating Temperature	0 ~ 40C	Unit Pack Wt.	1.55lb (0.72kg)
		Unit Wt.	Tx: 0.05lb (0.02kg), Rx: 0.30lb (0.12kg)