

Computer Power Cord - C19 to C20, 14 AWG, 10 ft

Product ID: PXTC19201410



This C19 to C20 power cord from StarTech.com features 14 AWG wire that's suitable for high-power connections, making it perfect for server applications and connecting to a Power Distribution Unit (PDU).

Plus, you can use the cable to extend the reach of your existing power cord by 10 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the PXTC19201410 power cord is backed by our lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 10 feet

Features

- Rated to carry 250V at 15A
 - 14 AWG wire
 - UL, RoHS compliant
-

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	IEC 60320 C19 Power
Connector B	IEC 60320 C20 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	250 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Weight of Product	18.9 oz [535 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	2.0 in [51 mm]
Shipping (Package) Weight	19.1 oz [542 g]



**What's in the
Box**

Included in Package	10 ft 14 AWG Computer Power Cord - C19 to C20
---------------------	---

****Product appearance and specifications are subject to change without notice.***

