

Computer Power Cord - C19 to C20, 14 AWG, 3 ft

Product ID: PXTC19C20143



This C19 to C20 power cord from StarTech.com features 14 AWG wire that's suitable for high power connections, making it perfect for server application and connecting to a Power Distribution Unit (PDU).

Plus, you can use the cable to extend the reach of your existing power cord by 3 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the PXTC19C20143 power cord is backed by our lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 3 feet

Features

- Rated to carry 250V at 15A
 - 14 AWG wire
 - UL, RoHS compliant
-

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	IEC 60320 C19 Power
Connector B	IEC 60320 C20 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	250 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]
Weight of Product	8.0 oz [228 g]

Packaging Information

Package Quantity	1
Package Length	11.4 in [29 cm]
Package Width	5.7 in [14.5 cm]
Package Height	2.2 in [56 mm]
Shipping (Package) Weight	8.3 oz [234 g]



**What's in the
Box**

Included in Package 3 ft 14 AWG Computer Power Cord - C19 to C20

****Product appearance and specifications are subject to change without notice.***

