

Computer Power Cord - NEMA 5-15P to C19, 14 AWG, 10 ft

Product ID: PXT515191410



This NEMA 5-15P-to-C19 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for high-end server equipment such as routers, switches, Power Distribution Units (PDU), etc.

Plus, you can use the cable to extend the reach of your existing power cord by 10 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXT515191410 power cord is backed by a lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Connect your high-power server equipment to a power outlet
- Extend your existing power cord by 10 feet

Features

- Rated to carry 125V at 15A
 - 14 AWG wire
 - UL, RoHS compliant
-

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	NEMA 5-15 Power (North America)
Connector B	IEC 60320 C19 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Weight of Product	17.3 oz [490 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	2.0 in [50 mm]
Shipping (Package) Weight	17.6 oz [500 g]



**What's in the
Box**

Included in Package 10 ft 14 AWG Computer Power Cord - NEMA 5-15P to IEC 320 C19

****Product appearance and specifications are subject to change without notice.***

