



GUS434

# 4x4 USB 3.0 Peripheral Sharing Switch

IOGEAR's 4x4 USB 3.0 Peripheral Sharing Switch provides a convenient means to share four USB devices between four different computers. A simple press of the button changes the connection of four USB devices such as keyboard, mouse, printer, portable hard drives, etc. from one computer to another.



## Features

---

- Share four USB peripheral devices between four computers
- Easily switch devices from one computer to another with the press of a button
- USB 3.0 compliant, supporting data transfer rates of up to 5Gbps
- LED indicates which computer is active
- Over-current protection
- Supports hot-plugging which allows easily add or remove computers connected to the installation without having to power down the switch
- Optional Micro USB cable can be connected to support additional power (up to 2.5W via USB 2.0 Port, up to 4.5W via USB 3.0 Port)

## Requirements

---

- Windows® 7, 8/8.1, 10, 11
- Mac OS X 10.3+
- Chrome OS™
- Linux-based systems
- Available USB 3.0 port

## Package Contents

---

- 1 x 4x4 USB 3.0 Peripheral Sharing Switch
- 4 x USB 3.0 Cables
- 1 x Selector Button
- 1 x Quick Start Guide
- 1 x Warranty Card



## Specifications

| FUNCTION                 | GUS434  | DIMENSIONS              | GUS434           |
|--------------------------|---|-------------------------|------------------|
| Computer Connections     |   | POP Information         |                  |
| Direct                   | 4   | 10" Peg Hook            | 3                |
| Port Selection           | Remote control selector button  | 6" Peg Hook             | 2                |
| Switches                 |   | Unit Dimensions         |                  |
| Port Selection           | Remote Console Selector Button x 1  | Height                  | 3.75" (9.53cm)   |
| LEDs                     |   | Length                  | 3.75" (9.53cm)   |
| Port Status              | White   | Depth                   | 1.06" (2.69cm)   |
| Connectors               |   | Unit Package Dimensions |                  |
| Computer Side            | USB 3.0 Type B x 4  | Height                  | 6.25" (23.50cm)  |
| USB                      | USB 3.0 Type A x 4  | Length                  |                  |
| Power                    | USB 3.0 Type Micro B (optional)   | Width                   | 6.5" (16.51cm)   |
| Operating Temperature    | 32 ~ 104F (0 ~ 40C)   | Depth                   | 2.875" (7.30cm)  |
| Storage Temperature      | -4 ~ 140F (-20 ~ 60C)   | Master Carton           |                  |
| Humidity                 | 0~80%   | Height                  | 7.5" (19.05cm)   |
| Housing                  |   | Width                   | 16" (40.64cm)    |
| Case                     | Plastic   | Depth                   | 9.375" (23.81cm) |
| Cable Length             | 72" (182.88cm)  | Master Carton Qty.      | 6                |
| Cable Type               | USB 3.0 Type B to A x 4   | Weight                  |                  |
| Power Consumption        | DC 5V, 1.69W  | Master Carton Wt.       | 8.9 lb (4.04 kg) |
| Operating System Support | Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Mac OS X 10.3+, Chrome OS?, Linux-based systems | Unit Pack Wt.           | 1.35 lb (0.6 kg) |
|                          |   | Unit Wt.                | 0.30lb (0.136kg) |