



C2G
3ft (0.9m) Value Series™ F-Type RG6 Coaxial Video Cable
Part No. CG-29131



Ordinary, "included in the box" f-type cables often use low quality materials with inferior shielding, and that can result in poor picture quality. Constructed from 75 Ohm coaxial cable to deliver high quality video, this cable can deliver all the detail, color and brightness you expect from your audio/video components. Ideal for connecting digital cable boxes, DSS receivers or any video source with f-type outputs to any TV with matching f-type inputs.

Low loss 18 AWG copper-clad steel conductor wire and polyethylene dielectric provide accurate picture resolution and color. A foil and double-braid shield protects against unwanted noise and interference. The 24K gold-plated heavy duty connectors ensure long-lasting, corrosion-free connections. The flexible PVC jacket enables easy installation while fully molded connectors provide excellent strain relief to keep your cable intact.

Features & Benefits

Use to connect a digital cable box, DSS receiver or any F-Type device to a TV
Perfect replacement cable for long length applications

Available in lengths up to 100ft

Specifications

General Info

Product Line	C2G	UPC Number	757120291312
Country Of Origin	China	Application Sector	Residential, Commercial
Warranty Type	Lifetime	Type	Cable

Dimensions

Cable Length	3 ft
--------------	------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	Flexible PVC	Wire Gauge	18 AWG
Cable Type	Video	Jacket Rating	Standard Non-Rated
Adapter Rear	F-Type Male	Adapter Front	F-Type Male