

Portable Server Rack with Handles - 9U

Product ID: RK960CP



This 9U portable server rack lets you store your server, network and telecommunications equipment in a sturdy mobile rack that has a fixed depth of 23 inches. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

With built-in handles and four swiveling casters, this mobile rack is easy to transport around your server room, office or studio. Its increased mobility makes this cabinet the ideal solution for telecommunication racks that need to interface with different equipment around your workspace.

The server rack features heavy-gauge mounting rails to ensure a stable installation platform. This durable 4-post rack supports a static loading capacity of up to 220 lb (99.8 kg), and is compliant with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494), providing a universal design that's compatible with most rack equipment.

Save time and hassle with a rack that's easy to put together. With its easy four-step assembly process, you can set this portable rack up in minutes.

The RK960CP is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Create a portable video editing and production rack that you can move around your studio to interface with different equipment
- Store this mobile rack beneath a table or bench in small offices or workspaces
- Mount equipment in technology shops and repair centers where security is required

Features

- Maximum portability with built-in handles and four swiveling casters included
- 9U closed-frame design
- TAA compliant for GSA Schedule purchases
- 23 in. mounting depth
- Supports a static loading capacity of 220 lb (99.8 kg)
- Easy-to-assemble with simple four-step installation

Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	9U
Special Features	Casters (Included)
	Easy Assembly
	U-Markings
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	220.6 lb [99.8 kg]
------------------------------	--------------------

Physical Characteristics

Color	Black
-------	-------

Product Measurements

Product Length	23.6 in [60 cm]
----------------	-----------------



Product Width	20.3 in [51.5 cm]
Product Height	18.8 in [47.7 cm]
Weight of Product	53.2 lb [24.1 kg]
Maximum Mounting Depth	23.4 in [59.5 cm]
Product Height with Casters	22.1 in [56.2 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	33.0 in [83.8 cm]
Package Width	28.7 in [73 cm]
Package Height	5.8 in [14.7 cm]
Shipping (Package) Weight	61.5 lb [27.8 kg]

What's in the Box

Included in Package	Side panel with handles
	Top panel
	Bottom panel
	Plastic cornercaps
	M5 (10 mm)Phillips flat-headscrew
	M3 (8 mm)Phillips flat-headscrew
	2.5 in. caster
	2.5 in. brakecaster
	M5 (15 mm)bracket screws
	M5 (12 mm)panel screws
M5 cage nut	



Cage nut tool

Phillips screwdriver

Phillips bit

Instruction manual

****Product appearance and specifications are subject to change without notice.***

