

DC Power Adapter - 5V, 3A

**Product ID:** SVA5M3NEUA



This replacement power adapter can provide a power source for any electronic device with an M-type barrel requiring up to 5 volts and 3 amps of power.

The adapter is a perfect replacement for the lost or damaged power adapter you've used to power your existing electronics.

For frequent travelers, this power adapter saves you from buying multiple adapters. To ensure it will work in your region and the region you're traveling to, the power adapter features 100-240V automatic switching and regional clips for North America, Europe, United Kingdom and Australia.

The SVA5M3NEUA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Replace a lost or broken power adapter
- Keep an extra power adapter on hand for your mission-critical devices
- Use a single power adapter as you travel between multiple regions

### Features

- Wide compatibility in different regions with 100-240V automatic switching and power clips included for North American, European, United Kingdom and Australian wall plugs

- Supports a range of devices that require 5 volt and 3 amps (or less) of power and an M-type barrel connector
- Reduces downtime in the event of a failure, by keeping a spare power adapter on-hand

---

**Power**

|                              |                     |
|------------------------------|---------------------|
| Warranty                     | 2 Years             |
| Power Source                 | AC Adapter Included |
| Input Voltage                | 100 - 240 AC        |
| Input Current                | 0.8 A               |
| Output Voltage               | 5 DC                |
| Output Current               | 3 A                 |
| Center Tip Polarity          | Positive            |
| Plug Type                    | M                   |
| Power Consumption (In Watts) | 15                  |

---

**Environmental**

|                       |                           |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 40C (32F to 104F)   |
| Storage Temperature   | -20C to 70C (-4F to 158F) |
| Humidity              | 10% - 80 % RH             |

---

**Physical Characteristics**

|                   |                  |
|-------------------|------------------|
| Product Length    | 3.5 in [89.0 mm] |
| Product Width     | 1.8 in [46.0 mm] |
| Product Height    | 1.4 in [36.0 mm] |
| Weight of Product | 5.6 oz [160.0 g] |

---

**Packaging Information**

|                |                  |
|----------------|------------------|
| Package Length | 4.9 in [12.4 cm] |
| Package Width  | 0.6 in [16.0 mm] |
| Package Height | 2.0 in [51.0 mm] |



|                              |                  |
|------------------------------|------------------|
| Shipping (Package)<br>Weight | 8.4 oz [238.0 g] |
|------------------------------|------------------|

---

**What's in the  
Box**

|                     |                             |
|---------------------|-----------------------------|
| Included in Package | power adapter (NA/EU/UK/AU) |
|---------------------|-----------------------------|

---

***\*Product appearance and specifications are subject to change without notice.***

