

High Speed HDMI Cable M/M - Active - CL2 In-Wall - 30 m (100 ft.)

Product ID: HDMM30MA



This active HDMI cable offers a connection distance of up to 100 feet (30 meters) between your HDMI enabled devices. It meets CL2 rating safety requirements, so it's ideal for in-wall cable runs in your home and office installations.

The cable features built-in amplifier circuitry which actively boosts your HDMI signal, with no external power required. It's the perfect solution for longer transmissions without any signal loss.

The HDMI cable is CL2 rated for in-wall installations, which makes them perfect for A/V installations in residential or office settings. You can set up your home theatre, gaming or audio-video equipment with the cables hidden away safely inside the walls and place your devices as needed throughout your work or living space.

This high-quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high-definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMM30MA is backed by StarTech.com's 2-year Warranty for guaranteed reliability.

Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the Source and Display labels on the HDMI connectors in order to ensure that the device and the HDMI source are connected properly.

Certifications, Reports and Compatibility

Applications

- Connect your high-definition A/V devices such as streaming media players (Roku, Apple TV), game consoles (Xbox One, PS4), Blu-Ray Disc or DVD players over long distances, with no signal loss

Features

- Built-in, active amplifier circuitry for longer connections
- CL2-rated for in-wall installations
- Supports Ultra HD Resolutions up to 4k x 2k

Hardware

Warranty	2 Years
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CL2 Rated
Chipset ID	Redmere - RM1691

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	98.4 ft [30 m]
Cable OD	0.3 in [8.5 mm]
Product Length	98.4 ft [30 m]
Weight of Product	5.1 lb [2.3 kg]

Packaging



Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	13.2 in [33.5 cm]
Package Height	3.1 in [80 mm]
Shipping (Package) Weight	5.8 lb [2.6 kg]

What's in the Box

Included in Package	30m Active CL2 In-Wall High Speed HDMI Cable - HDMI - M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***

