

10/100Mbps Ethernet to USB 2.0 Network LPR Print Server

Product ID: PM1115U2



This palm-sized print server makes it easy to share a USB printer with users on your network. It's the ideal solution for home or small office networks.

Enjoy cost-efficient network printing for multiple users. The USB 10/100 Mbps print server lets you share one USB printer with multiple users on your network, instead of having to buy separate printers for each individual workstation.

With web-based management, you can set up and monitor the printer server through a web browser, so you can place your printer at any convenient shared location - there's no need to put your printer next to your computer. You can send print jobs to another user in your home or office, or even to a printer in another country.

Compact and lightweight, the print server is easy to install with its straightforward installation wizards and remote web-based management. You simply use a USB cable to connect the print server to your printer's USB port, then use an RJ45 networking cable to connect it to the rest of your network.

The printer server supports the Line Printer Remote (LPR) protocol which enables Internet printing. It also supports Bonjour Print Services, making it easier to find and configure printers on your network.

The PM1115U2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Allows multiple users on an Ethernet network to share one USB printer
- Provides a reliable network printing solution for home, small office, educational and government institutions and any other environments that require printer sharing



Features

- Share a single USB printer with multiple users over a network
- Print from any network computer, across the office
- Provides a reliable Ethernet connection with 10Base-T/100Base-TX auto-sensing
- Compliant with USB 2.0
- Compatible with most standard printers
- Easy to configure using Windows based setup program or web-based management
- Supports LPR network printing, Bonjour Print Services
- Full-duplex support
- Jumbo frame support
- Auto MDI-X support
- Compact housing

| Hard | ware |
|------|------|
|------|------|

Warranty 2 Years

Ports

Industry Standards Compliant with IEEE 802.3 10BASE-T and IEEE 802.3u 100BASE-TX

Chipset ID EST - EST2862B

Performance

Maximum Data Transfer

100 Mbps

Rate

Max Distance 100 m / 330 ft

Remote Management

Ability

Yes

Auto MDIX Yes

Full Duplex Support Yes

Jumbo Frame Support 9K max.

Supported Protocols LPR



Connector(s)

External Ports RJ-45

USB Type-A (4 pin) USB 2.0

Software

OS Compatibility Windows XP, 7, 8 / RT, 10

Windows Server 2003, 2008 R2, 2012

Mac OS 10.6 to 10.10

Special Notes / Requirements

System and Cable Requirements

Printer with USB connection

USB printer cable not included

Note OS Compatibility refers to the included software only - the Print Server

itself can be used without software on most platforms that support

network printing

Indicators

LED Indicators Power

Link

Activity

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 0.25

Output Voltage 5 DC

Output Current 1A

Center Tip Polarity Positive

Plug Type H

Power Consumption (In

Watts)



Environmental

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -10C to 70C (14F to 158F)

Humidity 10% ~ 90% RH

Physical Characteristics

Color Black

Material Plastic

Product Length 2.1 in [53 mm]

Product Width 2.1 in [54 mm]

Product Height 0.9 in [23 mm]

Weight of Product 2.2 oz [62 g]

Packaging Information

Package Length 8.5 in [21.5 cm]

Package Width 5.9 in [14.9 cm]

Package Height 2.1 in [54 mm]

Shipping (Package)

Weight

11.5 oz [326 g]

What's in the Box

Included in Package USB 2.0 network LPR print server

universal power adapter (NA/JP, UK, EU, ANZ)

RJ45 network cable

quick start guide

software CD

^{*}Product appearance and specifications are subject to change without notice.