

# PMAX-0204



Heavy Duty Outdoor Housing with Heater and Fan (110V) and Bracket


## ► Specifications

### Device

Product Type	Box Camera Housing
Description	Heavy Duty Outdoor Housing with Heater and Fan (110V) and Bracket



### General

Power Source	AC 110V
Weight	3061.5g (6.75lb)
Dimensions	(W x H x D): 462.7mm x 171mm x 256mm (18.22" x 6.73" x 10.08")
Environmental Casing	Weatherproof (IP68), Vandal proof metal casing (IK10)
Fan	Yes
Heater	Yes
Operating Temperature	-30°C ~ 50°C (-22°F ~ 122°F)
Approvals	CE, IP68, IK10 (metal casing)
Color	White
Material	Aluminum
Warranty	1 Year(s). For extended warranty offering, see <a href="http://www.acti.com/support/warranty">http://www.acti.com/support/warranty</a>





## ▶ Related Products

### Box - Box

E217		2MP Video Analytics Box with D/N, Extreme WDR, SLLS, Fixed lens, f2.93mm/F2.0 (HOV:101.3°), H.264, 1080p/60fps, 2D+3D DNR, Audio, MicroSDHC/MicroSDXC, PoE/DC12V, DI/DO, RS-422/RS-485, Built-in Analytics
E23		2MP Box with D/N, Basic WDR, SLLS, Vari-focal lens, f2.8-12mm/F1.4 (HOV:88.4°-35.7°), DC iris, H.264, 1080p/30fps, DNR, PoE

### Box - Zoom Box

B26		3MP Video Analytics Zoom Box with D/N, Extreme WDR, SLLS, 36x Zoom lens, f4.6-165.6mm/F1.55-5.0 (HOV:57.6°-2.35°), DC iris, Auto Focus, H.265/H.264, 1080p/60fps, 2D+3D DNR, Audio, MicroSDHC/MicroSDXC, PoE/DC12V, DI/DO, RS-422/RS-485, Built-in Analytics
I29		2MP Video Analytics Zoom Box with D/N, Extreme WDR, ELLS, 36x Zoom lens, f4.6-165.6mm/F1.55-5.0 (HOV:62.7°-2.7°), DC iris, Auto Focus, H.264, 1080p/60fps, 2D+3D DNR, Audio, MicroSDHC/MicroSDXC, PoE/DC12V, DI/DO, RS-422/RS-485, Built-in Analytics

