

10 pack HPE J4859C Compatible SFP Module - 1000BASE-LX - 1GbE Single Mode /Multi Mode Fiber Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 10km - 1310nm - DDM HPE 1400, 1700, 1820

Product ID: J4859C10PKST



The J4859C10PKST is a ten-pack of our HP J4859C compatible fiber transceiver module that has been designed, programmed and tested to work with HP brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-LX compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1310 nm
- Maximum Data Transfer Rate: 1.25 Gbps
- Type: Single Mode / Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 3,092,408 hours
- Power Consumption: Less than 1 Watt
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

- Replacing defective or damaged SFP modules in HP switches and routers
- Expand your network to remote segments

Features

- 100% HPE J4859C COMPATIBLE: 10 pack SFPs work with HPE switches like 1400, 1700, 1820, 2520, 2530 and others
- TECHNICAL SPECS: 1000BASE-LX 1Gbps Single Mode (SMF)/Multi Mode (MMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in HPE routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- LIFETIME WARRANTY: Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

Warranty	Lifetime
Compatible Brand	HPE
Industry Standards	IEEE 802.3z 1000BASE-LX

Performance

Maximum Data Transfer Rate	1.25 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode / Multi Mode
Wavelength	1310nm
Fiber Operating Mode	Full-Duplex
DDM	Yes

Compatible Networks	1000 Mbps (1 Gbps)
MTBF	3,092,408 hours
Power Consumption (In Watts)	< 1 W

Connector(s)

Local Unit Connectors	Fiber Optic LC Duplex
-----------------------	-----------------------

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	30~75% RH

Physical Characteristics

Product Length	2.2 in [57.0 mm]
Product Width	0.6 in [14.0 mm]
Product Height	0.5 in [13.0 mm]
Weight of Product	6.0 oz [171.0 g]

Packaging Information

Package Length	4.9 in [12.5 cm]
Package Width	7.2 in [18.2 cm]
Package Height	1.5 in [37.0 mm]
Shipping (Package) Weight	8.0 oz [227.0 g]

What's in the Box

Included in Package	SFP transceivers
---------------------	------------------

**Product appearance and specifications are subject to change without notice.*

